

## The Combined Times Newsletter - February 2019

[Home](#) | [Products](#) | [Contact Us](#)

### PRODUCT SPOTLIGHT



EMR BDA/UDA Systems provide two-way UL/DL filtering and amplification of RF signals in buildings, tunnels, or areas that are shaded from adequate RF signal coverage. These are stand-alone, NFPA Compliant units encased in red NEMA 4 enclosures for optimal protection from harsh environmental conditions. Our BDAs operate on 115 VAC with options for power including 220 VAC, 13.6 VDC as well as UPS/Battery backup.

[840622 BDA Spec Sheet](#) / [Browse Category](#)



EMR BDAMON Series BDA Power Monitor provides remote monitoring consisting of a microprocessor controlled unit which monitors power supply, primary AC voltage, battery DC voltage, DC current, and door status alarm for up to four RF power amplifiers installed in any EMR signal enhancement system.

[BDAMON02 Spec Sheet](#) / [Browse Category](#)



EMR Bi-Directional and Uni-Directional Line Taps handle up to 250W power with coupler lengths corresponding to operating frequencies for unrivaled efficiency and reliability. EMR directional couplers are available in three and four channel varieties, factory tuned per application.

[2592/T-B Line Tap Spec Sheet](#) / [Browse Category](#)

### MEET THE TEAM!

Since joining EMR in 1993, Tracy Trujillo has worked in every production department.



For the past 3 years, Tracy has worked in our Systems Design Division where he has put his in-depth knowledge of the EMR product line to great use, always starting with a listening ear to customer requirements in order to design a solution to meet their needs. In his free time, Tracy enjoys spending time with his wife and 17 year old son, playing guitar, and working on his 1965 Ford Mustang. As loyal AZ Cardinals fans, he and his family and have been season ticket holders for decades. Now that's what you call sticking by your team through good and bad!

[More About EMR Corp](#)



All EMR products backed by 5 year warranty  
and are proudly Made in the USA!



EMR will be  
attending the  
IWCE Conference  
2019

[Click here for your Free  
Hall Passes Compliments  
of EMR!](#)

## TECHINCAL RECAP

Class A and Class B System Performance  
*From: 700/800 MHz LTE/Public Safety White Paper.*

A "Class B" Broadband BDA design doesn't require reprogramming if channels are changed or upgraded as long as additional channels are added within the operational pass bandwidth. The authority having jurisdiction avoids any ongoing requirement for detailed reprogramming and maintenance of records if frequencies are changed due to systems capacity or interference needs ....

[Read More](#)

## UPCOMING EVENTS



**IWCE Conference**

*March 4-8th 2019*

*Las Vegas Convention Center*

Receive free 2 day hall passes to  
the event compliments of EMR  
Corp!

[Click Here](#)

## EMR Recommended Training Sessions @ IWCE 2019

**Components Review: It's the Little Things That Count**

Alan Leffler, N7WYE - EMR Corp - Sales Manager- Americas

Tuesday, 03/05/2019: 1:30 pm - 2:15 pm

Room: N258 - Session Number: T238

[See details](#)

## DAS and BDA Design, Installation and Maintenance

Ira Wiesenfeld, P.E. - IWA Technical Services, Inc. - Principal Engineer

Monday, 03/04/2019: 9:00 am - 5:00 pm

Room: N232 - Session Number: DAS

[See details](#)

For more information on this news release contact [sales@emrcorp.com](mailto:sales@emrcorp.com)

